

# PA200DS-BR

## 200 mm Semi-automatic Probe System with Blue Ray



### DATA SHEET

The PA200BD-BR was specifically designed for measurements requiring backside access to the wafer. The design allows you free access to both sides of the wafer, as well as high throughput due to a lightweight chuck design. The wafer itself can be fixed by vacuum or mechanically clamped to allow testing up to the substrate edge.

The system's precision ensures smooth probe landing with safe, repeatable electrical contact. In combination with the unique Z-profiling function, even extreme variations in height can be compensated. This reduces pad damage and easily allows devices to be bonded after testing, even with the thinnest of pads. At the same time, the systems's accuracy eliminates the need for a time-wasting probe mark inspection.

Flexibility and modularity are the keys for your production testing needs and has created a solution that allows adapting a wide range of instrumentation and accessories to the probe system. To further enhance productivity and ease-of-use, Cascade Microtech has designed a communication between the hardware and software of the PA200DS-BR that accommodates high-speed communication using the Ethernet interface or an optional TTL interface.

### FEATURES / BENEFITS

High throughput	Highest Z-axis resolution of any production probe system
Double-side probing	Stable, Linux-based controller with optional TTL or GPIB interfaces Manual or motorized holder for backside measurement equipment
Modularity	Variety of wafer carriers, glass chucks, mechanical edge clamping solutions Wafer handling robot can be docked onto probe system Easy to integrate with ProberBench™ Operating Environment VisionModule™ available for automated testing processes
Cost effectiveness	Interfaces to all major analysis instrumentation, optics software, and testers Smallest footprint Low cost of ownership Fast return on investment Grows with your requirements

## SPECIFICATIONS\*

### Chuck Stage

<b>X-Y Movement</b>	Closed-loop DC servo with linear encoder feedback
Travel / Resolution	205 mm x 205 mm / 1.0 $\mu$ m
Repeatability / Accuracy	$\pm$ 2.0 $\mu$ m / $\pm$ 5.0 $\mu$ m
Minimum cycle time	250 ms (1000 $\mu$ m step size, 250 $\mu$ m separation), depending on index and chuck configuration
<b>Z Movement</b>	DC servo with linear encoder feedback
Travel / Resolution	15 mm / 0.25 $\mu$ m
Repeatability	$\pm$ 1.0 $\mu$ m
<b>Theta Movement</b>	DC servo with linear encoder feedback
Travel / Resolution	$\pm$ 6.0° / 0.0001°

### Utilities

Power	115 / 230 V, 50 / 60 Hz, 600 W (maximum 1500 VA), depending on tool configuration
Vacuum	< 200 mbar abs., 8 mm
Compressed air	4 bar minimum, 8 mm

### Microscope

Fits to video and stereo microscopes

### Positioner Platen

Vacuum

### Chucks

Standard	200 mm stainless steel, RF capable with two integrated AUX sites
Thermal	200 mm, 25° C to 150° C (only PA200A BlueRay)

### Optional Accessories

BlueRay prober table	With optional shelf for measuring instrument, monitor and keyboard Optional VIT701 with vibration isolation
Wafer handling robot	One cassette for wafers from 50 mm to 100 mm or 75 mm to 200 mm, including cassette scanner and prealigner
Electronics interfaces	TTL, GPIB
Software	ProberBench CorePackage™ with WaferMap, VisionModule, VideoTracker™, Programmer Tools, ShapeTracker, Z-Profiling
Electronic/optical measuring	Fiber optic, integration sphere, large area detector
Backside equipment stage	Manual 10 mm x 10 mm x 10 mm or motorized 25 mm x 25 mm x 25 mm, for integrating sphere, fiber optics or customized equipment
CCD camera	B/W, color
Operating lamp	3 color

## PHYSICAL DIMENSIONS

### Dimensions (WxDxH)

Mechanics	700 mm x 880 mm x 750 mm
With wafer handling robot	1150 mm x 880 mm x 1500 mm (including table)
Electronics	450 mm x 400 mm x 230 mm
Joystick controller	280 mm x 250 mm x 140 mm

### Weight


Mechanics / Electronics	250 kg / 13 kg
-------------------------	----------------



AP200DS BlueRay, equipped with wafer handling robot and integrated alignment camera.



Mechanical wafer clamping for probing to the wafer's edge.



Vacuum wafer fixation on transparent glass chuck for fragile substrates.

© Copyright 2011 Cascade Microtech, Inc.  
All rights reserved. Cascade Microtech is a registered trademark, and ProberBench, VisionModule, CorePackage and VideoTracker are trademarks of Cascade Microtech, Inc. All other trademarks are the property of their own respective owners.

Data subject to change without notice

**Cascade Microtech, Inc.**  
**Corporate Headquarters**  
toll free: +1-800-550-3279  
phone: +1-503-601-1000  
email: [cmi\\_sales@cmicro.com](mailto:cmi_sales@cmicro.com)

**Germany**  
phone: +49-811-60005-0  
email: [cmg\\_sales@cmicro.com](mailto:cmg_sales@cmicro.com)

**Japan**  
phone: +81-3-5615-5150  
email: [cmj\\_sales@cmicro.com](mailto:cmj_sales@cmicro.com)

**China**  
phone: +86-21-3330-3188  
email: [cmc\\_sales@cmicro.com](mailto:cmc_sales@cmicro.com)

**Singapore**  
phone: +65-6873-7482  
email: [cms\\_sales@cmicro.com](mailto:cms_sales@cmicro.com)

**Taiwan**  
phone: +886-3-5722810  
email: [cmt\\_sales@cmicro.com](mailto:cmt_sales@cmicro.com)

PA200DSBR-DS-0911

PA200DS-BR

[www.cascademicrotech.com](http://www.cascademicrotech.com)

